



Pushing Performance  
Since 1945

# Han B Hood Side Entry HC 2 Levers M40



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 19 30 024 0538                                                                        |
| Specification      | Han B Hood Side Entry HC 2 Levers M40                                                 |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19300240538">https://b2b.harting.com/19300240538</a> |

## Identification

|                          |                   |
|--------------------------|-------------------|
| Category                 | Hoods/Housings    |
| Series of hoods/housings | Han® B            |
| Type of hood/housing     | Hood              |
| Type                     | High construction |

## Version

|                      |                                                   |
|----------------------|---------------------------------------------------|
| Size                 | 24 B                                              |
| Version              | Side entry                                        |
| Cable entry          | 1x M40                                            |
| Locking type         | Double locking lever (on the hood)                |
| Han-Easy Lock®       | Yes                                               |
| Field of application | Standard hoods/housings for industrial connectors |

## Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65                                           |
|                                        | IP66                                           |
|                                        | IP67                                           |
| Type rating acc. to UL 50 / UL 50E     | 4                                              |
|                                        | 4X                                             |
|                                        | 12                                             |



**Pushing Performance**  
Since 1945

## Material properties

|                                                            |                                                           |
|------------------------------------------------------------|-----------------------------------------------------------|
| Material (hood/housing)                                    | Aluminium die-cast                                        |
| Surface (hood/housing)                                     | Powder-coated                                             |
| Colour (hood/housing)                                      | RAL 7037 (dust grey)                                      |
| Material (locking)                                         | Polycarbonate (PC)<br>Stainless steel                     |
| Colour (locking)                                           | RAL 7037 (dust grey)                                      |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                                       |
| RoHS                                                       | compliant                                                 |
| ELV status                                                 | compliant                                                 |
| China RoHS                                                 | e                                                         |
| REACH Annex XVII substances                                | Not contained                                             |
| REACH ANNEX XIV substances                                 | Not contained                                             |
| REACH SVHC substances                                      | Yes                                                       |
| REACH SVHC substances                                      | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |
| California Proposition 65 substances                       | Yes                                                       |
| California Proposition 65 substances                       | Nickel                                                    |
| Fire protection on railway vehicles                        | EN 45545-2 (2020-08)                                      |
| Requirement set with Hazard Levels                         | R22 (HL 1-3)<br>R23 (HL 1-3)                              |

## Specifications and approvals

|           |              |
|-----------|--------------|
| Approvals | CE<br>DNV GL |
|-----------|--------------|

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 281 g                                    |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140126930                            |
| ETIM                           | EC000437                                 |
| eCI@ss                         | 27440202 Shell for industrial connectors |