




(SIMULATIVE NO. 200532-2)
類似 NO. 200532-2


H	REVISED PER ECO-20-007658	KR	MZ	12JUN 2020
G	REVISD	T.N	N.Y	09SEP 2011
F	改訂 (E100-0246-93)	Y.T	S.H	1/8/20
E	REVISED (0886910) 082-6797			1/8/20
E	ADDED -3 (P-DWG REVIE)			1/8/20
D	OBSOLETE -1 (P-DWG REVIE)			1/8/20
C	ADDED -2 (P-DWG REV. GZ)			1/8/20
C	REVISED			1/8/20
B	REVISED (P-DWG REVIE)			1/8/20
A	REVISED (P-DWG REVIE)			1/8/20
O	RELEASED (REV. A.)			1/8/20
L.T.R.	寫真 (REVISION RECORD)	DR.	CHK.	DATE

C-171050

[illegible]


(C) COPYRIGHT 2012 BY Tyco Electronics Japan G.K.		参考図面 (CUSTOMER COPY REFERENCE ONLY)	
材料 (MATERIAL) (SEE DWG.) 上参照	絶縁配線径 (WIRE RANGE)  mm ² (AWG)	 TE Connectivity	
仕上 (FINISH) (SEE DWG.) 上参照	被覆外径 (INSULATION DIA.)  mm (IN)	分類 (CLASS) 	型式 (TYPE) 
DR.	一般公差 (TOLERANCE EXCEPT AS NOTED)	公差 (SCALE) 	LOC 番号 (NO.) J B C-171050
CHK. <i>M. Iwano 7/30/11</i>	公差 (SCALE) ±0.4 ±1.0	公差 (SCALE) 	REV H
DE.	名称 (NAME) 50極 180°	名称 (NAME) ショート シールド	名称 (NAME) (50 POS 180° SHORT SEALED)
APP. <i>etc abin</i>	名称 (NAME) 50極 180°	名称 (NAME) ショート シールド	名称 (NAME) (50 POS 180° SHORT SEALED)

(NOTE)
 注記: 1. 最大電線束線径: $\phi 18$. (MAX. CABLES DIA.: $\phi 18$)
 2. 最小電線束線径: $\phi 12$. (MIN. CABLES DIA.: $\phi 12$)
 3. △ ウィスカー対策・RoSH対応品
 (WHISKER COUNTERMEASURE & RoSH COMPLIANCE)



OBSOLETE

3"




(SHORT SEALED)
 ショートシールド (171050-3のみ)
 (寸法は 171050-2 と同じ)

④
 ポリエステルテープ
 外側両面貼リ付け
 (POLYESTER TAPE)

21.6REF	22.6REF	21.8REF	21.8REF	21.8REF	寸法	品名	材質	備考
2	2	2	2	2	10.8±0.3	SCREW FILLISTER HEAD	△ CARBON STEEL, NI PLATED	⑤
2	2	2	2	2	11.3±0.3	SCREW FILLISTER HEAD	CARBON STEEL, ZINC PLATED	⑤
2	2	2	2	2	10.8±0.3	POLYESTER TAPE	POLYESTER TAPE	④
2	2	2	2	2	10.8±0.3	CABLE CLAMP	△ ZINC-COATED STEEL, PAINTED TO METALIC SILVER	③
2	2	2	2	2	10.8±0.3	CABLE CLAMP	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	③
2	2	2	2	2	10.8±0.3	SHIELD HALF(STAMPED)	△ ZINC-COATED STEEL, PAINTED TO METALIC SILVER	②
2	2	2	2	2	11.3±0.3	SHIELD HALF(STAMPED)	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	②
2	2	2	2	2	10.8±0.3	SHIELD HALF(STAMPED)	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	②
2	2	2	2	2	10.8±0.3	SHIELD HALF(STAMPED)	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	②
2	2	2	2	2	10.8±0.3	SHIELD HALF(STAMPED)	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	②
2	2	2	2	2	10.8±0.3	SHIELD HALF	△ ZINC-COATED STEEL, PAINTED TO METALIC SILVER	①
2	2	2	2	2	11.3±0.3	SHIELD HALF	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	①
2	2	2	2	2	10.8±0.3	SHIELD HALF	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	①
2	2	2	2	2	10.8±0.3	SHIELD HALF	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	①

3"

21.6REF



④
 ポリエステルテープ
 外側両面貼リ付け
 (POLYESTER TAPE)

④
 ポリエステルテープ
 外側両面貼リ付け
 (POLYESTER TAPE)

21.6REF	22.6REF	21.8REF	21.8REF	21.8REF	寸法	品名	材質	備考
2	2	2	2	2	10.8±0.3	SCREW FILLISTER HEAD	△ CARBON STEEL, NI PLATED	⑤
2	2	2	2	2	11.3±0.3	SCREW FILLISTER HEAD	CARBON STEEL, ZINC PLATED	⑤
2	2	2	2	2	10.8±0.3	POLYESTER TAPE	POLYESTER TAPE	④
2	2	2	2	2	10.8±0.3	CABLE CLAMP	△ ZINC-COATED STEEL, PAINTED TO METALIC SILVER	③
2	2	2	2	2	10.8±0.3	CABLE CLAMP	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	③
2	2	2	2	2	10.8±0.3	SHIELD HALF(STAMPED)	△ ZINC-COATED STEEL, PAINTED TO METALIC SILVER	②
2	2	2	2	2	11.3±0.3	SHIELD HALF(STAMPED)	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	②
2	2	2	2	2	10.8±0.3	SHIELD HALF(STAMPED)	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	②
2	2	2	2	2	10.8±0.3	SHIELD HALF(STAMPED)	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	②
2	2	2	2	2	10.8±0.3	SHIELD HALF(STAMPED)	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	②
2	2	2	2	2	10.8±0.3	SHIELD HALF	△ ZINC-COATED STEEL, PAINTED TO METALIC SILVER	①
2	2	2	2	2	11.3±0.3	SHIELD HALF	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	①
2	2	2	2	2	10.8±0.3	SHIELD HALF	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	①
2	2	2	2	2	10.8±0.3	SHIELD HALF	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	①