


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	7/12/99	

- ADAPTER, 6/4mm SPADE LUG WITH 4mm BANANA JACK.
- SPECIFICATIONS:
INSULATOR: POLYACETAL
SPADE BODY: BRASS, NICKEL PLATED
- RATING:
CURRENT: 36A MAX.
RESISTANCE: <1mΩ.
TEMPERATURE: -20° C TO +80° C.



PART NUMBER

CT2553-#

COLOR: 0 — BLACK
2 — RED
4 — YELLOW
5 — GREEN
6 — BLUE
9 — WHITE

THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING		CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
		MATERIAL		APPROVALS		DATE		6/4mm SPADE LUG ADAPTER w/4mm JACK	
		FINISH		DRAWN WDH		7/12/99			
NEXT ASSY		USED ON		CHECKED		ENGR.		TITLE	
APPLICATION				DESIGN ACTIVITY				SIZE A CAGE CODE 43F45 DWG. NO. P255300 REV. —	
								SCALE 1:1 SHEET 1 OF 1	