







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	12APR2021	J.S	I.Y
	A1	ECN-21-117700	15SEP2021	J.S	Z.Z

D



DETAIL Z
SCALE 5:1



B

A

2388280-1 AS SHOWN

1. MATERIAL : PA6-GF30 V-0 OR EQUIVALENCE RESIN.
- 2 PRODUCT DATE
- 3 LETTER-INSERTFOR THE REVISION STATUS OF THE MOULD
- 4 MATERIAL MARKING ACCORDING TO VDA260
5. BULK PACKAGING IN CORRUGATED BOX
- 6 MOULD CAVITY MARKING
- 7 TE LOGO
- 8 WARGAGE PERMITTED UP TO -1.5MM FROM NOMINAL SIZE
9. SUITALBE FOR TAB HOUISNG WITH FLANGE GROUP E, SEE PRODUCT GROUP DRAWING 1563709.
- 10 MARKING FOR SUITABLE SHEET METEAL THICKNESS(NOMINAL SIZE)

D

C

B

A

2388280-7	A	SLIDER 3.5MM	GREY	8.4	12.4	8.0	8.1
2388280-6	A	SLIDER 3MM	YELLOW	8.9	12.6	8.5	8.4
2388280-5	A	SLIDER 2.5MM	RED	9.4	13.4	9.0	8.6
2388280-4	A	SLIDER 2MM	VIOLET	9.9	13.9	9.5	8.9
2388280-3	A	SLIDER 1.6MM	GREEN	10.3	14.3	9.9	9.1
2388280-2	A	SLIDER 1.5MM	GREY	10.4	14.4	10.0	9.2
2388280-1	A	SLIDER 1.2MM	ORANGE	10.7	14.7	10.3	9.3
PART NO	REV.	DESCRIPTION	COLOUR	DIM X	DIM Y	DIM Z	WEIGHT [g]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHANG 25MAR2021	TE Connectivity				
DIMENSIONS: mm		CHK C. WAN 25MAR2021					
		APVD J. YIN 25MAR2021	NAME SLIDER GROUP E,TAB HOUSING				
		PRODUCT SPEC 108-94020					
		APPLICATION SPEC 114-18756					
MATERIAL PA6-GF30 V-0		WEIGHT SEE TABLE A2	SIZE A2	CAGE CODE 00779	DRAWING NO C=2388280	RESTRICTED TO	
		RESTRICTED CUSTOMER			SCALE 1:1	SHEET 1 OF 1	REV A1