

Coaxial PCB Connector
82_MBX-S50-0-24/111_N

Description

Straight PCB jack

Interface Standards
HUBER+SUHNER MBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	surface mount
---------------------	---------------

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	PA (Polyamide)	
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing	DOU-00249323
Catalogue drawing	DCA-00262074
Mounting hole	DOU-00142408

Ordering Information

Tape and Reel package	82_MBX-S50-0-24/111_NM
Single package	82_MBX-S50-0-24/111_NE
Bulk 100 pcs package	82_MBX-S50-0-24/111_NH

Remarks

PCB connector with stand-offs