

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-21-112460	2SEP2021	TL	HL

D

C

B




A

D

C


B

A



NOTES:

- 1 MATERIAL:
CONTACTS & SHIELD: COPPER ALLOY
HOUSING: GLASSFILLED POLYESTER,COLOR NATURAL
- 2 GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
1,27µm NICKEL MIN. AND EON PIN: 0,5µm TIN MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- 3 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
- 4 ASSEMBLY PRINTED WITH P/N AND DATECODE
- 5 HOLE PATTERN FOR FEMALE CONNECTOR
PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
- 6 ROW "f" 4 PLATED THROUGH HOLES FOR UPPERSHIELD



2/3	1	2367982-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY LI 14JAN2020	TE Connectivity Ltd.			
		CHK ALEX SHOAL 14JAN2020				
		APVD HOPE LU 14JAN2020	NAME			
		PRODUCT SPEC 108-60123	Z PACK 2mm HM 8 COLUMNS PRE-SHIELDED RECEPTACLE			
		APPLICATION SPEC 114-19029	-			
MATERIAL		WEIGHT 0	SIZE A2	CAGE CODE 00779	DRAWING NO C-2367982	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 1	REV B	