

OPEN-BOTTOM SOCKET CONTACTS

RELIABILITY, ROBUSTNESS, AND FLEXIBILITY





preci-dip

PRECI-DIP SOCKET CONTACT WITH CLIP

A proven and customizable solution for your connections

Off the shelf PRECI-DIP Clips
Over 50 references available

Customizable or standard
Screw-Machined Socket
Designed and built in-house




Automatic assembly in-house
100% Quality check


ADVANTAGES OF OPEN-BOTTOM SOCKET

A wide range of possibilities


Independence of pin length
Compensates tolerances



Guiding chamfer
Facilitate mating



Stackable design
Flexibility



Tape and reel packaging
Facilitates handling




Fully Customizable

Short lead time for production parts




A complete range

From 0.38mm to 2.45 mm mating pin, up to 20Amps



Low profile solution

Cost effective



MANY APPLICATIONS

MEDICAL, AUTOMOTIVE, MIL-AERO, INDUSTRIAL AND CONSUMER

