

BU-2241-D-XX-@

(Multiple Feature Test Prod to Right-Angle Shrouded Banana Plug)



- BU-2241-D is a multiple feature test prod to right-angle shrouded banana plug.
- Hookup wire is 18 AWG 65/36 tinned copper with 90°C-resistant PVC insulation.
- Material:

Needle	Stainless steel
Banana Plugs	Nickel-plated brass
Housing	ABS
- Ratings:

Current	20 Amps
Voltage	1000V, CAT II
- Length: The "XX" in the model number indicates wire length in inches.
Available lengths: 48" (others available upon request)
- Color: The "@" in the model number indicates color.
Available colors : -0 Black, -2 Red
- RoHS 3 compliant