






CONTACT PLATING	PART-NO.
SIGNAL CONTACTS GOLD FLASH over NICKEL	3H15W4SAM62A10X
HIGH POWER CONTACTS PLATING MATING AREA: GOLD FLASH over NICKEL PLATING TERMINATION SIDE: GOLD FLASH over NICKEL	
SIGNAL CONTACTS 30µin HARD GOLD over 50µin NICKEL	3H15W4SCM42A10X
HIGH POWER CONTACTS PLATING MATING AREA: 30µin HARD GOLD over min. 50µin NICKEL PLATING TERMINATION SIDE: GOLD FLASH over NICKEL	



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: SEE TABLE
SOLDER CUP ACCEPTS CABLE AWG 22
- HIGH POWER CONTACTS 20A: COPPER ALLOY
PLATING: SEE TABLE
SOLDER CUP ACCEPTS CABLE AWG 12-14
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										tolerance			 dim. in mm	scale: 2:1 (5:1)						
														material: SEE NOTES						
														date	name		title: D-SUB HD COMBINATION FEMALE 15W4S SOLDER CUP			
														drawn	26.05.10	Lehmenkühler				
														appd.	26.05.10	Koch				
				norm																
				d-old			dwg no: 13K1A3221			DIN-A3										
a	Origin									sh: 1										
rev.	description	date	name				part no: SEE TABLE													

DIN-A3
sh: 1