




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	CI91496	2019-08-27	NianPing Yu	Add UL Label
C	CI92063	2019-12-03	NianPing Yu	△XI

ALTW
CONFIDENTIAL
2019-12-03
R&D DEPT.

RECOMMENDED P.C.B. LAYOUT
GENERAL TOLERANCE IS ±0.05


- Notes:
- * Ⓞ Important Dimension To Check.
 - * Housing: High temperature thermoplastic.
UL94V-0, color is Natural white.
 - * Pickup Cap: High temperature thermoplastic.
UL94V-0, color is Natural white.
 - * Terminal: Copper Alloy, Gold Plated on contact area. Tin plated on solder tails.
 - * Solder Peg: Copper Alloy, Tin plated over Nickel.

UNIT:mm		TITLE
TOLERANCE		SSL-1.1 DC 4P JACK CONN, WITH POST,S/T,SMT TYPE
.X ±0.25		SCALE 5:1
.XX ±0.1		SIZE A4
.XXX ±0.05		SHEET 1 OF 2
ANGLES ±1°		REV. C
		WC-REV. A.3
		QC: Inspection item


Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	SSL11-J4A00-000001	DRAWN BY	NianPing Yu	DATE	2019-08-27
DWG NO	SSL11-J4A00-000001	CHECKED BY	Fisher Wang	DATE	2019-08-27
CUSTOMER	ALTW	APPROVED BY	Max Yang	DATE	2019-08-27

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



1. 400Pcs Per Reel
2. 8 Reel Per Carton (3200Pcs/Carton)
3. Reference Standard: EIA-481-D
4. Net Weight: 0.7Kg/Carton.
5. Gross Weight: 4.1Kg/Carton.



A	UNIT: mm				TITLE SSL-1.1 DC 4P JACK CONN, WITH POST, S/T, SMT TYPE			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO SSL11-J4A00-000001		DRAWN BY NianPing Yu		DATE 2019-08-27			
	TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°				SCALE 5:1		SIZE A4			SHEET 2 OF 2		DWG NO SSL11-J4A00-000001		CHECKED BY Fisher Wang		DATE 2019-08-27	
					REV. C		WC-REV. A.5		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Max Yang		DATE 2019-08-27		
1		2		3		4		5		6		7		8		W10814-03-西01A2	