





- 1
- LOW-INSERTION FASTON TERMINALS, BASE P/N 63306, ARE USED IN THIS PRODUCT.
- 2
- TIN PLATE PER .002032 [.000080] MIN PER MIL-T-10727.
- 3
- MATERIAL: HOUSING - 6/6 NYLON
TERMINAL - BRASS
- 4
- FINISH: HOUSING - COLOR, NATURAL
TERMINAL - SEE TABLE

OBSOLETE	BULK	 TIN PLATE	2.79-4.32 [.110-.170] DIA	0.8-2.0 mm ² [18-14]	0.813 [.032]	-5-520963-2-					
	BULK	PLAIN				5-520963-1					
	STANDARD	 TIN PLATE				520963-2					
	STANDARD	PLAIN				520963-1					
PACKAGING		TERMINAL FINISH	INSULATION RANGE	WIRE SIZE	MATING TAB THK ±0.025 [±.001]	PART NO.					
			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH	6/27/89	 TE Connectivity				
					CHK MS FEHER	6/27/89					
			DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R KUZO	6/27/89	NAME ASSEMBLY, ULTRA-POD, RECEPTACLE, 6.35 [.250] SERIES		
					0 PLC ± -		PRODUCT SPEC				
					1 PLC ± -		108-1285				
					2 PLC ± -		APPLICATION SPEC				
					3 PLC ± 0.25 [.010]		114-2124		SIZE A2		
					4 PLC ± -		WEIGHT -				
			MATERIAL 		FINISH 		CUSTOMER DRAWING		DRAWING NO C-520963		
						RESTRICTED TO -					
									SCALE 5:1		
						SHEET 1 of 1					
									REV R3		