

## Coaxial Panel Connector 22\_BNC-50-0-2/133\_N

### Description

Straight bulkhead receptacle jack

Interface standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

#### Mechanical Data

Number of matings	500
Weight	0.0118 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLADE (R) Plating
Body	Brass	SUCOPLADE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLADE (R) Plating
Washer	Bronze	SUCOPLADE (R) Plating

### Related Documents

Outline drawing	DOU-00011593
Catalogue drawing	DCA-00011595
Mounting hole	DOU-00010700

### Ordering Information

Single package	22_BNC-50-0-2/133_NE
----------------	----------------------

### Remarks

equipped with insulating washers 77 Z-0-0-2