

SUMMARY

Wires

Low voltage 11



Image is for illustrative purpose only

Series 3P
Termination type Male crimp
IP rating 61
AWG wire size 30.00 - 22.00
Cable Ø 6.70 - 7.50 mm
Status active

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model FG*: Straight plug with key and cable seal
Keying User configurable, 1 of 11 key positions. Plug: male contacts; Receptacle: female contacts
Housing Material PSU (Polysulfone), black
Weight 21.34 g

Performance

Configuration 3P.310 : 10 Low Voltage + 1 Ground contact
Insulator L: PEEK (UL 94 / V-0/1.5)
Rated Current 5 Amps

Specifications


Contact Type: Special

Others

Endurance (Shell): >1000 mating cycles
Temp (min / max): -50°C / +150°C
F ret (min): 100 N
F ret (max): 200 N
Steam sterilization: 20 times (with potting on rear connection)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS



Dimensions

	A	L
mm.	21.2	63
in.	0,83	2,48

RECOMMENDED BY LEMO

Tools

- Crimp settings:
- AWG/Selector = 20-22-24/6-5-5
- Replacement contact:
- FGG.3P.560.ZZC / EGG.3P.661.ZZY

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.