

SUMMARY

Wires

Image is for illustrative purpose only

| Series | OF | Download |
|------------------|-------------------------|---------------------------------|
| Termination type | No contacts / Accessory | Request a quote |
| IP rating | 0 | Catalog |
| AWG wire size | 0.00 - 0.00 | |
| Cable Ø | 3.80 - 9.00 mm | |
| Status | active | |

TECHNICAL DETAILS

Mechanics

| | |
|-------------------|-----------|
| Shell Style/Model | *: |
| Keying | No keying |
| Housing Material | |
| Weight | .30 g |

Performance

| |
|---------------|
| Configuration |
| Insulator |
| Rated Current |

Others

Temperature range in water steam: +140°C

DRAWINGS

No keying

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.