



Pushing Performance
Since 1945

Han 3A-HTE, 9-17mm, PC black +glued seal



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 003 0418
Specification	Han 3A-HTE, 9-17mm, PC black +glued seal
HARTING eCatalogue	https://b2b.harting.com/19200030418

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Hood
Description of hood/housing	for Han-Brid [®] With glued seal With integrated cable gland

Version

Size	3 A
Version	Top entry
Cable entry	1x Integrated
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance
Since 1945

Technical characteristics

Cable diameter	9 ... 17 mm
----------------	-------------

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	10
Net weight	17.24 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140164161
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors