


LOC		DIST		ZONE		L/TN		REVISIONS		DATE	
6	14										
								DESCRIPTION		REVISED PER 0720-0230-93	
								A		2/28/93	

METRIC
DIMENSIONS LISTED IN mm [INCHES]

WIRE RANGE		E13288 Listed	
12-10 AWG STRANDED		12-10 AWG STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
NOT CERTIFIED		NOT APPLICABLE	

△ STAMP AMP 12-10* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE: 170°C MAX

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN INCHES
TOLERANCES ON:
2 PLG DEC ± .005
3 PLG DEC ± .010
ANGLES ± .5°

DR 1-28-93
TA BRINKMAN
CHK 1-28-93
DA PATTERSON
APPO 1-28-93
DE MILLER
APPO 1-28-93
JL HECLEY
PRODUCT SPEC

AMP
AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RECTANGULAR
TONGUE, BUDGET

SIZE CAGE CODE DRAWING NO
C 00779 C-327953

WEIGHT SCALE 10:1 SHEET 1 OF 1