

Han 3HPR-C-TL-with cord-black chrome



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 003 5402
Specification	Han 3HPR-C-TL-with cord-black chrome
HARTING eCatalogue	https://b2b.harting.com/09400035402

Identification

Category	Accessories
Series of hoods/housings	Han® HPR
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings With fixing cord

Version

Size	3 A
Locking type	Toggle locking

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Black chrome coating
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	not compliant

Material properties

ELV status	not compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	10
Net weight	49 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140057135
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors