

SUMMARY

Wires



| | |
|-------------|---|
| Low voltage | 3 |
|-------------|---|

Image is for illustrative purpose only

| | |
|------------------|--------------------------------|
| Series | 0K |
| Termination type | Male solder |
| IP rating | 68 |
| AWG wire size | 28.00 - 20.00 |
| Cable Ø | 3.10 - 3.50 mm |
| Status | active |
| Matching parts | EGG.0K.303.CLL |

Download

[Request a quote](#)
[Eplan](#)
[Catalog](#)

TECHNICAL DETAILS

Mechanics

| | |
|-------------------|---|
| Shell Style/Model | FG*: Straight plug, cable collet and nut for fitting a bend relief |
| Keying | 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Housing Material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Variant | Z : Nut for fitting a bend relief |
| Weight | 12.41 g |

Performance

| | |
|---------------|---------------------------|
| Configuration | 0K.303 : 3 Low Voltage |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 8 Amps |

Specifications

| | |
|--------------------------|-------------------------------|
| Contact Type: | Solder |
| Contact Dia.: | 0.9 mm (0.035in) |
| Bucket Dia.: | 1.0 mm (0.039in) |
| Max. Solid Conductor: | 0.56 mm ² (AWG 20) |
| Max. Stranded Conductor: | 0.56 mm ² (AWG 20) |
| R (max): | 4.8 mOhm |


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest (contact-shell): 900 V (AC), 1300 V (DC)
Vtest (contact-contact): 1200 V (AC), 1700 V (DC)

Others

Endurance (Shell): 5000 mating cycles
Temp (min / max): -55°C / +200°C
Humidity (max): <=95% [at 60 deg C /140 F]
Vibration: 15 g [10 Hz - 2000 Hz]
Shock Resistance: 100 g [6 ms]
Climatical Category: 50/175/21
Shielding (min): 95 dB (10 MHz)
Shielding (min): 80 dB (1 GHz)
Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

| | A | L | M | S2 |
|-----|------|------|------|------|
| mm. | 11 | 34 | 23 | 7 |
| in. | 0,43 | 1,34 | 0,91 | 0,28 |

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Spanner wrench: [DCD.0E.007.PA070](#)

Caps: [BFG.0K.100.NAS](#)

Cables

| | | | |
|--------------------|-----|-------|---|
| CMN.03.T28.031PGCE | PVC | GREY |  |
| CMN.03.T28.031PGZE | | Grey |  |
| CMN.03.T28.031PNCE | PVC | Black |  |
| CMN.03.T28.031PNZE | | |  |
| 30141 | PVC | Grey |  |
| 3081 | PVC | Black | |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.