

Illuminated pushbutton Ø 16 mm silver contact

82-4152.1114



<https://eao.com/p/82-4152.1114>

Your product:



82-4152.1114
Illuminated pushbutton Ø
16 mm silver contact

FRONT

Front bezel shape:	flush
Front bezel material:	Stainless steel

MOUNTING

Mounting cut-out:	Ø 16 mm
--------------------------	---------

OPERATING-/INDICATION PART

Lens optics:	opaque
Shape of illumination:	Ring
Lens colour:	Silver
Illumination colour:	Red
Lens illumination:	illuminative
Lens shape:	flush
Lens material:	Stainless steel

ELECTRICAL CHARACTERISTICS

Pollution degree:	2, according to EN IEC 60947-1
Rated insulation voltage Ui:	250 V
Contacts:	1 C
Operating voltage:	24 V AC/DC
Switching voltage and switching current:	

according to IEC 60947-5-1 (Silver contacts)	
Service categorie AC-15	
Voltage	Current
24 VAC	1 A
35 VAC	1 A (M12 version)
110 VAC	1 A
220 VAC	0.5 A
Switch rating DC service categorie DC-13 (Silver contacts)	
Voltage	Current
24 VDC	0.7 A
35 VDC	0.5 A (M12 version)
110 VDC	0.2 A
220 VDC	0.1 A

according to UL 508 (Silver contacts)	
$\cos\phi$ 0,75 ... 0,8	
Voltage	Current
120 VAC	5 A
240 VAC	3 A
24 VAC	1 A

Rated Operational Voltage Ue:

250 VAC

Thermal current Ith:

5 A

Electrical lifetime:

50 000 cycles of operation

Electric strength:

1500 VAC, 50 Hz 1 minute between life terminals and ground

MECHANICAL CHARACTERISTIC

Tightening torque:	0.5 ... 0.6 Nm, Screw terminal 0.1 Nm
Contact material:	Silver
Mechanical lifetime:	1 Mio. cycles of operation
Switching action:	Momentary
Operating force:	4 N ... 7 N
Operating Travel:	ca. 3 mm
Terminal:	Screw terminal
Weight:	0.018 kg
Switching system:	Snap-action switching element

AMBIENT CONDITION

Shock resistance:	Max. 500 m / s ² as per IEC 60068-2-27
Climate resistance:	Damp heat, 21 days according to IEC 60512-11
Operating temperature:	- 30 °C ... + 70 °C
IP front protection:	IP65, IP67
Storage temperature:	

– 40 °C ... + 80 °C

Vibration resistance:

10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6

CERTIFICATE

Conformities:

CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

Approbations:

CB, CCC, C UL, UL

OTHER


Kind of illumination:

Single-LED

Short Description:


Illuminated pushbutton Ø 16 mm silver contact, Momentary, 24 V AC/DC, 1 C, Screw terminal, Stainless steel, Red, Silver

Dimension drawings:




A = Solder terminal
B = Screw terminal

Wiring diagrams:



Mounting cut-outs:



Component layouts:

