

Han 3M AK



Image is for illustration purposes only. Please refer to product description.

Part number	09 37 003 5403
Specification	Han 3M AK
HARTING eCatalogue	https://b2b.harting.com/09370035403

Identification

Category	Accessories
Series of hoods/housings	Han [®] M
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings
	for surface mounted housings
	for cable to cable housing
	Metal
	With fixing cord

Version

Size	3 A
Locking type	Single locking lever
Details	for mounted male insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
	IP67

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
-----------------------	---------------

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	23.9 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140191884
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors