






版数 VER.	年月日 DATE	CN NO.	変更内容 DESCRIPTION	製図 DR.	担当 CHK.	査閲 APPD.	承認 APPD.
------------	-------------	--------	---------------------	-----------	------------	-------------	-------------



A
(5 : 1)



NOTE 1. THESE CONTACTS ARE SUPPLIED IN REEL. THERE ARE 6000 CONTACTS PER REEL.
NOTE 2. APPLICABLE CABLE: AWG#22 TO #24, INSULATION OUTER DIAMETER: $\phi 0.9\text{mm}$ TO $\phi 1.5\text{mm}$.
NOTE 3. PRODUCTION DATE IS SHOWN.
NOTE 4. FORM IDENTIFICATION MARK IS SHOWN.
NOTE 5. PRODUCT NAME, DRAWING NUMBER AND QUANTITY ARE SHOWN.
NOTE 6. MATING AREA: GOLD PLATING OVER NICKEL, TERMINAL AREA: TIN PLATING OVER NICKEL
OTHER AREA: NICKEL PLATING

注1. 本コネクタは6000個巻きのリールにて供給される。
注2. 適用電線:AWG#22~#24、被覆外径: $\phi 0.9\sim 1.5\text{mm}$
注3. 図示の位置に製造年月を表示する。
注4. 図示の位置に形状識別記号を表示する。
注5. 図示の位置に品名、図番、数量を表示する。
注6. 接触部:ニッケル上金めっき、結線部:ニッケル上錫めっき、その他:ニッケルめっき

3	TAPE	1	PAPER	-	-
2	REEL	1	PAPER	-	-
1	SOCKET CONTACT	6000	COPPER ALLOY	NOTE 6	-
符号 NO.	名 称 DESCRIPTION	個 数 QTY.	材 料 MATERIAL	仕 上 FINISH	備 考 REMARKS

仕様書 (SPECIFICATION) JACS-11204		第1版 (ORIGINAL DATE) 25/APR/2017		尺度 (SCALE) 1:10	シリーズ (SERIES) HB01	日本航空電子工業株式会社	JAE JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.	図面番号 (DRAWING NO.) SJ118796	版数 (VER.) 1
一般公差 (GENERAL TOLERANCE) 寸法 (DIMENSION)		製図 DR.	—	名称 (TITLE) HB01S06K4P3 SOCKET CONTACT #22		図面番号 (DRAWING NO.) SJ118796			
±0.8 × ±0.4 ×× ±0.1 ××× ±		担当 CHK. 査閲 APPD. 承認 APPD.	K. NAKAZAWA — T. KUDOU	質量 (MASS) —					
角度 (ANGLES) ×° ± ×°×' ±		単位 (UNIT) : mm							

S/W