



DFN-6 to DIP-10 SMT Adapter (0.65 mm pitch, 2.5 x 2.5 mm body)




REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		1.30				
B		0.80				
C		0.35				
B2		0.70				
C2		2.00				
D		0.30				
D2		0.30				
E		0.65				
F					0.300	
G					0.100	
H					0.025	




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)