

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-18-000456	09JAN2018	MD	MD

- 1 TO ENSURE PROPER MATING OF RECEPTACLE TO TAB, TAB LENGTH ON PLUNGER SWITCH SHOULD BE A MINIMUM OF 8.25 [.325].
- 2 MATERIAL IS UL94 V0 AND 150°C RATED.
- 3 ACCEPTS .187 SERIES BUDGET FASTON STRAIGHT RECEPTACLES SUCH AS P/N 63477-X
- 4 ACCEPTS .110 SERIES POSITIVE-LOCK MARK III STRAIGHT RECEPTACLES FOR .032" THK TAB, P/N 1742975-1.

D

D

C



C

B




B

A

A



SCALE 4:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. DIDONATO CHK M. DIDONATO APVD T. DING	21MAY16 - 21MAY16	TE Connectivity		
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ± 1 PLC ± 2 PLC ±0.25 [.010] 3 PLC ± 4 PLC ± ANGLES ± FINISH		HOUSING, RECEPTACLE, 187 FASTON, WITH .110 POSI-LOCK, DOOR SWITCH		
MATERIAL 6/6 NYLON		COLOR-BLACK		SIZE A2	CAGE CODE 00779	DRAWING NO. C-1969843
				RESTRICTED TO -		
				SCALE 5:1	SHEET 1 OF 1	REV B1