

Han TC300 male contact M8, short



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 7579
Specification	Han TC300 male contact M8, short
HARTING eCatalogue	https://b2b.harting.com/09110007579

Identification

Category	Contacts
Series	TC 300
Type of contact	Screw contact
Description of the contact	M8 Short version

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Rated current	≤300 A
Contact resistance	≤0.3 mΩ
Tightening torque	10 Nm
Wrench size	14
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant
ELV status	compliant

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	1
Net weight	40 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188532
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors