





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS |     |                          |         |     |      |
|-----|------|-----------|-----|--------------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION              | DATE    | DWN | APVD |
| FT  | 0    |           | A1  | REVISED PER ECO-06-17112 | 7/18/06 | SS  | SRY  |

1. MATERIAL: 0.80[.032] THICK, BRASS TEMPERED.
2. FINISH: BRIGHT TIN PLATE.



|                    |             |
|--------------------|-------------|
| 90°/45°, DBL SIDED | 1776860-4   |
| 90°, DBL SIDED     | 1776860-3   |
| 45°, DBL SIDED     | 1776860-2   |
| FLAT, DBL SIDED    | 1776860-1   |
| DESCRIPTION        | PART NUMBER |

|                                        |  |                                           |                              |                                                                                                |                                                      |  |           |              |            |                 |               |           |  |
|----------------------------------------|--|-------------------------------------------|------------------------------|------------------------------------------------------------------------------------------------|------------------------------------------------------|--|-----------|--------------|------------|-----------------|---------------|-----------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  |                                           | DWN<br>S SCHLEGEL<br>6/20/06 | <b>tyco</b><br><b>Electronics</b><br>Tyco Electronics Corporation<br>Harrisburg, PA 17105-3608 |                                                      |  |           |              |            |                 |               |           |  |
|                                        |  |                                           | CHK<br>S YODER<br>6/20/06    |                                                                                                |                                                      |  |           |              |            |                 |               |           |  |
| DIMENSIONS:<br>mm [INCHES]             |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED: |                              | APVD<br>S YODER<br>6/20/06                                                                     | NAME<br>.250 QC TABS, DOUBLE SIDED, 9.5mm DOUBLE ROW |  |           |              |            |                 |               |           |  |
|                                        |  | 0 PLC ± -                                 |                              | PRODUCT SPEC                                                                                   | -                                                    |  |           |              |            |                 |               |           |  |
|                                        |  | 1 PLC ± 0.3                               |                              | -                                                                                              | -                                                    |  |           |              |            |                 |               |           |  |
|                                        |  | 2 PLC ± 0.25                              |                              | APPLICATION SPEC                                                                               | -                                                    |  |           |              |            |                 |               |           |  |
|                                        |  | 3 PLC ± -                                 |                              | -                                                                                              | SIZE                                                 |  | CAGE CODE |              | DRAWING NO |                 | RESTRICTED TO |           |  |
|                                        |  | 4 PLC ± -                                 |                              | -                                                                                              | A2                                                   |  | 00779     |              | C=1776860  |                 | -             |           |  |
|                                        |  | ANGLES ± 5'                               |                              | WEIGHT                                                                                         | -                                                    |  |           |              |            |                 |               |           |  |
| MATERIAL<br>-                          |  | FINISH<br>-                               |                              | CUSTOMER DRAWING                                                                               |                                                      |  |           | SCALE<br>2:1 |            | SHEET<br>1 of 1 |               | REV<br>A1 |  |