

Data sheet

US2:CLMHCAK11

product brand name	CLM 300-400A,AUX CONT KIT,1NO/1 For CLM 300-400A contactor
design of the product	Class CLM
product type designation	1 Normally Open and 1 Normally Closed
special product feature	Aux contacts
For use on Class CLM 300 and 400 Amp lighting contactors	
General technical data	
weight [lb]	0.01 lb
Height x Width x Depth [in]	2.44 x 0.98 x 1.38 in
touch protection against electrical shock	no touch protection
ambient temperature [°F]	
• during storage	-67 ... +176 °F
• during operation	-31 ... +167 °F
ambient temperature	
• during storage	-55 ... +80 °C
• during operation	-35 ... +75 °C
country of origin	USA
Contact block	
number of NC contacts / for auxiliary contacts	1
number of NO contacts / for auxiliary contacts	1
Mounting/wiring	
fastening method	laterally mounted
type of electrical connection	screw-type terminals
tightening torque [lbf·in] / with screw-type terminals	8 ... 12 lbf·in
type of connectable conductor cross-sections / for AWG cables / for control connection / with screw-type terminals / single or multi-stranded	2x (12 ... 16 AWG)
temperature / of the conductor / for control connection / with screw-type terminals / maximum permissible	75 °C
material / of the conductor	CU
Certificates/ approvals	
certificate of suitability	cULus
Further information	
Industry Mall (Online ordering system)	https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:CLMHCAK11
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)	https://support.industry.siemens.com/cs/ww/en/ps/US2:CLMHCAK11
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)	http://www.automation.siemens.com/bilddb/cax_us.aspx?mlfb=US2:CLMHCAK11&lang=en

last modified:

9/14/2022 