


DO NOT SCALE

DIMENSIONS IN INCH

INCH

THIRD ANGLE
PROJECTION

REV REVISION RECORD

DATE

DW

APD

A2

REVISED PER ECR-19-015041

05NOV2019

PC



MB

TO ACCEPT AWG 20 OR AWG 18 SOLID
OR FUSED STRANDED LEAD WIRENOTES 1 FOR MATING CAVITY SPECIFICATIONS REFER
TO APPLICATION SPEC. #114-2046

2 IDENTIFICATION NUMBER FOR SLOT SIZE "6"

3 SLOTS ACCEPT SINGLE OR DOUBLE AWG 30-27
CU MAGNET WIRE OR AWG 28-25 AL MAGNET
WIRE4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

5 REELED WITH INTERLEAVE PAPER.



4 OBSOLETE

150 mm

TINPLATED

BRASS

160899-5

12 mm

TINPLATED

BRASS

160899-4

REELWIDTH

FINISH

MATERIAL

PARTNUMBER

CUSTOMER
DRAWING

TE Connectivity

FOR REFERENCE ONLY
WILL NOT BE UPDATED

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION APRIL, 1985

© COPYRIGHT 19 86,87,88 BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED.
AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR
PATENTS PENDING.DR.
D.CAMPSCHROERDATE
30/05/85WIRE RANGE
3

NAME

MAG-MATE

REV. DATE
D M YCHK.
W.ESSER

DATE

INSUL. RANGE
-

POKE-IN TERMINAL

160388

APP.
L.VAN SOEST

DATE

SIZE
A3SHEET
1 OF 1

DWG. No.

160899

REV. LTR.
A2

8

7

6

5

4

3

2

1