








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	30DEC2015	DL	CW
	B	ECR-21-122216	09DEC2021	WQR	CW




H24BP-T6-M
T2071244101-000
DOCKING FRAME FOR HMN INSERTS_FLOATING
6 MODULES



OTHER SPEC REFER TO
PN T2071244101-000

H24BP-T6-F
T2071244201-000
DOCKING FRAME FOR HMN INSERTS_FIXED
6 MODULES

1. 技术参数：
 绝缘材料：PC
 阻燃等级：UL94V-0
 插拔次数：500次



PANEL CUT OUT

SPACING OF TWO PANELS AT CLOSE STATUS

T2071244201-000	H24BP-T6-F DOCKING FRAME FOR HMN INSERTS_FIXED HMN塑胶框架_固定端
T2071244101-000	H24BP-T6-M DOCKING FRAME FOR HMN INSERTS_FLOATING HMN塑胶框架_浮动端
PART NUMBER 料 号	PART DESCRIPTION 描 述

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 30DEC2015		 TE Connectivity	
		CHK CHRIS WANG 30DEC2015			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME H24BP-T6-M/F DOCKING FRAME FOR HMN INSERTS 6 MODULES	
mm		APVD XU XIANG 30DEC2015			
		PRODUCT SPEC 108-137168			
		APPLICATION SPEC 114-137168			
MATERIAL		FINISH		SIZE A2	CAGE CODE -
-		-		DRAWING NO C-T2071244X01000	
-		-		RESTRICTED TO -	
-		-		SCALE 4.5	
-		-		SHEET 1 OF 1	
-		-		REV B	
-		-		CUSTOMER DRAWING	