

PCB ADAPTER 5-POLE FOR Han DDD MODULE




Image is for illustration purposes only. Please refer to product description.

Part number	09 16 000 9915
Specification	PCB ADAPTER 5-POLE FOR Han DDD MODULE
HARTING eCatalogue	https://b2b.harting.com/09160009915

Identification

Category	Accessories
Type of accessory	PCB adapter
Description of the accessory	5 poles In the Han [®] DDD module

Version

Gender	Male Female
Details	for PCB's up to 1.6 mm

Technical characteristics

Rated current	7.5 A
Rated voltage	160 V
Rated impulse voltage	2.5 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C

Material properties

Material (insert)	Polyamide (PA)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	10
Net weight	2 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140023710
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)