










REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



3D View


PIN DEFINE TABLE			
PIN	SIGNAL	PIN	SIGNAL
A12	GND	B1	GND
A11		B2	
A10		B3	
A9	VBUS	B4	VBUS
A8	SBU1	B5	CC2
A7	D-	B6	D+
A6	D+	B7	D-
A5	CC1	B8	SBU2
A4	VBUS	B9	VBUS
A3		B10	
A2		B11	
A1	GND	B12	GND





(TOP VIEW)
 RECOMMENDED P.C.B. LAYOUT (T:1.0~1.2mm)
 TOLERANCE UNSPECIFIED ±0.05mm

SPECIFICATION:



- Material:
HOUSING&MOLDING:LCP,UL94 V-0
CONTACTS:COPPER ALLOY T=0.20mm
MIDDLE CLIP:SUS301-1/2H,T=0.15mm
SHELL:SUS, T=0.30mm
- Mechanical:
2.1.Mating force:5~20Nf Max.;
2.2.Unmating force:6~20Nf Min.;
2.3.Durability:10000 Cycles;
- Electrical:
3.1.Current Rating:3A Max.;
3.2.Voltage Rating:20V Max.;
3.3.Dielectric Withstanding voltage:100VAc;
3.4.Contact resistance:40m Ohms Max.;
3.5.Insulation Resistance:100M Ohms Min.;
- Environmental:
4.1.Operating temperature:-40°C~+85°C;
4.2.Wetting Temperature:265±5°C,5±0.5s

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X:±0.35	X.X':±3°	PART NO.	TITLE: TYPE-C 16pin母座板	
X.XX:±0.25	X.XX':±2°	TYPE-C-2MD-16P		上型带塑胶柱
X.XXX:±0.15		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia	 SCALE N:A	SHEET 1/2
MATERILA	---	APPD: Ava		
FINISH	---			

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



3D View



说明:

- 1.每卷前后各空16PCS,尾部用美纹胶纸封住;
- 2.将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
- 3.每10卷盘一叠共10000Pcs并装入1个外箱内;
- 4.在搬运过程中要轻拿轻放;
- 5.在运输中不可堆放过多(1.8M最高),不可重压;
- 6.跌落测试条件:

成品箱从1.2米高度自由落体(一角三棱六面):

- a.产品不可跑出下带凹槽;
- b.产品不可有摔伤,变形;
- c.内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY
①	TYPE C RECEPTACLE		10000PCS/CARTON
②	CARRIER TAPE	W=24mm,T=0.35mm	1000PCS/PLATE
③	COVER TAPE	W=21.5mm	10PLATES/CARTON
④	REEL PLATE	ø330*100*24.4mm	10PCS/CARTON
⑤	RoHS LABEL		10PCS/CARTON
⑥	PRODUCT LABER		10PCS/CARTON
⑦	CARTON	350*340*310mm	1PCS/PACKAGE

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X:±0.35	X.X':±3"	PART NO. TYPE-C-2MD-16P	TITLE: TYPE-C 16pin母座板上型带塑胶柱	
X.XX:±0.25	X.XX':±2"			
X.XXX:±0.15				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	---	CHED: Olvia		
FINISH	---	APPD: Ava		SCALE N:A
				SHEET 2/2