



Pushing Performance
Since 1945

Plug socket module UK (BS)



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 001 0006
Specification	Plug socket module UK (BS)
HARTING eCatalogue	https://b2b.harting.com/39500010006

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Socket
Specification	Finger safe

Version

Termination method	Screw termination
Field of application	Great Britain (BS)

Termination data

Supply voltage	250 V AC
Nominal current	13 A
Nominal frequency	50 Hz
	60 Hz

Technical characteristics

Conductor cross-section	4 mm ²
Mounting depth	30 mm

Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	78 g
Country of origin	Hungary
European customs tariff number	85366990
GTIN	5713140154919
ETIM	EC000450
eCl@ss	27144042 Plug socket