




1. PART NUMBER CHANGES AND/OR DESIGN CHANGES AFFECTING ITEM INTERCHANGEABILITY REQUIRE PRIOR TE APPROVAL AND AUTHORIZATION BY REVISION TO THIS DRAWING.
2. ITEMS PROVIDED TO THIS SPECIFICATION SHALL BE IDENTIFIED ON CONTAINER WITH THE FOLLOWING INFORMATION, PART NUMBER AND DATE CODE OF MANUFACTURE.
3. MATERIAL:

INSULATOR - POLYESTER, GLASS FILLED, UL94 V-O RATED, COLOR: BLACK

MODULE - METAL CASTING

CROWN - BeCu

CONTACT - BRASS
4. FINISH:

INSERT - SILVER PLATED .000200 MIN THK. OVER NICKEL .000040 MIN THK.

CROWN - GOLD PLATED .000030 MIN THK. OVER NICKEL .000040 MIN THK.
- 6643232-1

PART NUMBER

5

A FIVE POUND (5lb) FORCES REQUIRED TO CORRECTLY SEAT THE CONNECTOR WITH PLATED THRU HOLES LESS THEN Ø.040.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±.020
4 PLC	±-
ANGLES	±.5
FINISH	-

CUSTOMER DRAWING

DWN

18MAY2011

LOVATO/GRZYBOWSKI

CHK

D. ORRIS

APVD

18MAY2011

CHAU/ORRIS

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

NAME

ICCON SOCKET, PARALLEL 10 PIN FOOTPRINT, SOLDER STYLE

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-6643232

RESTRICTED TO

-

SCALE

4:1

SHEET

1

OF

1

REV

B