

	CLM AUXILIARY CONT.KITS,300-400 For CLM 300-400A contactor
product brand name	Class CLM
design of the product	2 Normally Closed
product type designation	Aux contacts
special product feature	For use on Class CLM 300 and 400 Amp lighting contactors
General technical data	
weight [lb]	0.01 lb
Height x Width x Depth [in]	2.44 × 0.98 × 1.38 in
touch protection against electrical shock	no touch protection
ambient temperature [°F]	
• during storage	-67 ... +176 °F
• during operation	-31 ... +167 °F
ambient temperature	
• during storage	-55 ... +80 °C
• during operation	-35 ... +75 °C
country of origin	USA
Contact block	
number of NC contacts / for auxiliary contacts	0
number of NO contacts / for auxiliary contacts	2
Mounting/wiring	
fastening method	laterally mounted
type of electrical connection	screw-type terminals
tightening torque [lbf-in] / with screw-type terminals	8 ... 12 lbf-in
type of connectable conductor cross-sections / for AWG cables / for control connection / with screw-type terminals / single or multi-stranded	2x (12 ... 16 AWG)
temperature / of the conductor / for control connection / with screw-type terminals / maximum permissible	75 °C
material / of the conductor	CU
Certificates/ approvals	
certificate of suitability	cULus
Further information	
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:CLMHCAK02	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/US2:CLMHCAK02	
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_us.aspx?mlfb=US2:CLMHCAK02&lang=en	

last modified:

9/14/2022 