

Han 3M-PFT-SL-M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 37 003 1120
Specification	Han 3M-PFT-SL-M20
HARTING eCatalogue	https://b2b.harting.com/19370031120

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M
Type of hood/housing	Panel feed through housing
Description of hood/housing	With seal

Version

Size	3 A
Version	Top entry
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Hoods/housings for rough environments
Pack contents	With seal screw

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)



Pushing Performance
Since 1945

Material properties

Material (seal)	NBR
Colour (seal)	Black
Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

Specifications and approvals

Approvals	CE
	DNV GL

Commercial data

Packaging size	10
Net weight	101 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140170995
ETIM	EC000437
eCI@ss	27440202 Shell for industrial connectors