





DESCRIPTION: M12 FEMALE - PANEL MOUNT (REAR) - 6 POS.



PANEL CUTOUT



NUT



NOTE:

MATERIAL

HOUSING:
CONTACT:
NUT:
SHELL:
O-RING:

PBT UL94V-0, BLACK
BRASS
BRASS
BRASS
EPDM, BLACK

FINISH

CONTACT:

GOLD PLATED
OVER 50µ" NICKEL
NICKEL PLATED
NICKEL PLATED

ELECTRICAL

RATED CURRENT:
RATED VOLTAGE:
INSULATION RESISTANCE:
CONTACT RESISTANCE:
WATER PROOF:

2A
30V
100 MΩhms MIN.
10 mΩhms MAX.
IP67


ENVIRONMENT

OPERATION TEMPERATURE: -40°C TO +85°C

860-006-213R00Y

3 = BRASS/NICKEL SHELL & NUT
S = STAINLESS STEEL SHELL & NUT

1 = GOLD FLASH
4 = 10µ" GOLD



PCB LAYOUT

RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

08-19-16

NorComp

SCALE:

NTS

SHEET

1

OF

1

REV

3

DWG NO.

860-006-213R00Y