

© COPYRIGHT 1977 NOT TO BE
INCORPORATED FOR PUBLICATION
ALL RIGHTS RESERVED
REPRODUCED AND INCORPORATED
WITHOUT PERMISSION BY U.S. AND
FOREIGN PATENTS AND/OR PATENTS
PENDING.

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED	P/F
0	ORIGINAL	5-11-77		0
A	ADDED -2	7-10-77	BA	✓


INCH MM

.010	0,25
.040	1,02
.110	2,79
.150	3,81
.165	4,19
.219	5,56
.223	5,66
.270	6,86
.276	7,01
.315	8,00

207457 -2 1. SAME AS -1 EXCEPT

2. PASSIVATED

207-57- WAS SHOWN



PART NO

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.
TOLERANCES ON:
DECIMALS $\pm .005$
ANGLES $\pm 0^\circ 30'$

CONTRACT NO

OR

CHK

APPD

APPD

DSGN APPD

OTHER APPD

MATERIAL

STAINLESS
STEEL

FINISH

11



AMP INCORPORATED
Harrisburg, Pa.

NAME

KEYING INSERT

SIZE

A

CODE IDENT NO

00779

DRAWING NO

207457

SCALE

11

SHEET

1 OF 1