

Pushbutton Ø 19 mm silver contact

82-5152.1000.B002



<https://eao.com/p/82-5152.1000.B002>

Your product:



82-5152.1000.B002
Pushbutton Ø 19 mm silver contact

FRONT

Front bezel material:	Stainless steel
Front bezel shape:	flush

MOUNTING

Mounting cut-out:	Ø 19 mm
-------------------	---------

OPERATING-/INDICATION PART

Lens illumination:	non illuminative
Lens optics:	opaque
Symbol:	Standby
Lens material:	Stainless steel
Lens shape:	flush
Lens colour:	Silver

ELECTRICAL CHARACTERISTICS

Switching voltage and switching current:	according to IEC 60947-5-1 (Silver contacts)	
	Service categorie AC-15	
	Voltage	Current
	24 VAC	1 A
	35 VAC	1 A (M12 versio
	110 VAC	1 A
	220 VAC	0.5 A
	Switch rating DC service categorie DC-13 (Silver contacts)	
	Voltage	Current
	24 VDC	0.7 A
	35 VDC	0.5 A (M12 vers
	110 VDC	0.2 A
	220 VDC	0.1 A

according to UL 508 (Silver contacts)

$\cos\phi$ 0,75 ... 0,8

Voltage

120 VAC

240 VAC

24 VAC

Current

5 A

3 A

1 A

Thermal current I_{th}:	5 A
Electric strength:	1500 VAC, 50 Hz 1 minute between life terminals and ground
Rated insulation voltage U_i:	250 V
Electrical lifetime:	50 000 cycles of operation
Pollution degree:	2, according to EN IEC 60947-1
Rated Operational Voltage U_e:	250 VAC

MECHANICAL CHARACTERISTIC

Operating force:	4 N ... 7 N
Switching action:	Momentary
Operating Travel:	ca. 3 mm
Switching system:	Snap-action switching element
Tightening torque:	0.5 ... 0.6 Nm, Screw terminal 0.1 Nm
Weight:	0.018 kg
Contact material:	Silver
Terminal:	Screw terminal
Mechanical lifetime:	1 Mio. cycles of operation

AMBIENT CONDITION

IP front protection:	IP65, IP67
Storage temperature:	– 40 °C ... + 80 °C
Shock resistance:	Max. 500 m / s ² as per IEC 60068-2-27
Climate resistance:	Damp heat, 21 days according to IEC 60512-11
Vibration resistance:	10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6
Operating temperature:	– 30 °C ... + 70 °C

CERTIFICATE


Approbations: CB, CCC, C UL, UL

Conformities: CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)


OTHER

Short Description: Pushbutton Ø 19 mm silver contact, Momentary, Screw terminal, Stainless steel, Standby, Silver

Wiring diagrams:




Dimension drawings:



A = Solder terminal
B = Screw terminal

Component layouts:



Mounting cut-outs:

