








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE3-910081	2009/01/16	Vicky	Update the drawing.
C	LEN13C0086	2013/12/06	Tony_leng	Change 3.3 To 3.5mm



Recommended Panel Cut-Out



Pin Assignments
Front View



Notes:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP67.
- * Connector: Black, Nylon+GF.
- * Female Pin: Copper Alloy, Gold Plated.
- * Gasket: Black, EPDM.
- * Nut: Copper Alloy, Nickel Plated.
- * Shield: Copper Alloy, Nickel Plated.
- * For Panel Thickness Max: 6.0mm.
- * Nut Torque: 4~6 Kgf.cm

UNIT:mm	
TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°

TITLE	M10.5 Conn Panel Screw 3P M Conn F Pin		
SCALE	2:1	SIZE	A4
REV.	C	WC-REV.	B.2
			$\varnothing$: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	105-03PMFS-SC7001	DRAWN BY	Tony_leng	DATE	2013-12-06
DWG NO	105-03PMFS-SC7001	CHECKED BY	Rensong	DATE	2013-12-06
CUSTOMER	ALTW	APPROVED BY	Jerry	DATE	2013-12-06