





LOC		DIST		REVISONS			
IR		P	LYR	DESCRIPTION	DATE	DWN	APVD
		E1		REDRAWN AS CD SUPERSEDED CR	02MAR2010	PKS	RRP
		E2		PN 1740240-3 ADDED AND -2 OBSOLETE PER PARTS STATUS	19DEC2011	PKS	RRP





- 1 NUMBERS 1 2 3 4 Max. HEIGHT 5mm. THICKNESS 0.2 mm
- 2 MATERIAL DESCRIPTION. CAVITY - NO EXCHANGEABLE HEIGHT 2 mm -THICKNESS 0.4MM. ACCORDING TO DIN 1451
- 3 THE IDENTIFICATION MARKS SHOULD BE MODIFIABLE USING DIE SLIDES
- 4 NOT DIMENSIONED RADIUS = 0.5
- 5 TE LOGO & TE PN ON TOP OF THE COVER.ATTENTION:PN SUFFIX EXCHANGEABLE
- 6 THE CONNECTOR SHOULD BE WITHOUT DEFECTS
- 7 MATERIAL: PA6 (GW T 750 °C WITHOUT FLAME)
- 8 VOLUME APPROX. 5700mm³
- 9 -
- 10 LOCATION CODE ACCORDING SPEC : 115-24
- 11 PA6.6. NOT RELEASED FOR PRODUCTION
- 12 MOISTURE CONTENT OF THE PARTS 2% - 3% for 11 1.5% - 2% for 7

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	Kishore M	10-Jan-05	 TE Connectivity						
				CHK	M.Offenloch	10-Jan-05							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	Th.Klenner	10-Jan-05	NAME HOUSING FOR CONNECTOR 4 POS						
mm		9 PLC ±0.1		PRODUCT SPEC		-							
		1 PLC ±		APPLICATION SPEC		-							
		2 PLC ±				SIZE							
		3 PLC ±				CAGE CODE							
		4 PLC ±				DRAWING NO							
		ANGLES				RESTRICTED TO							
MATERIAL		FINISH		WEIGHT		A1 00779 ©=1740240					-		
				CUSTOMER DRAWING		SCALE 4:1					SHEET 1 OF 2		
								REV E2					

LOC		DIST		REVISONS			
IR	-	P	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

PN 1740240-3 AS SHOWN
(ALL OTHER DIMENSIONS SHALL REMAIN SIMILAR TO PN 1740240-1)

DETAIL A
SCALE 10:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	SENTHIL	19DEC2011	TE Connectivity		
		CHK	SENTHIL	20DEC2011			
		APVD	RAJENDRA	21DEC2011	NAME	HOUSING FOR CONNECTOR 4 POS	
					SIZE	CAGE CODE	DRAWING NO
					A100779		©=1740240
					EUSTOMER DRAWING		SCALE 5:1 SHEET 2 OF 2 REV E2