

D

D

C


C

B

B

A

A



- 1

FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948. CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194, REAR GROMMET: FLUROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1.
- 2

PART TO MARKED WITH TE IDENTIFICATION, TE PART NO. AND DATE CODE: YEAR & WEEK (YY WW) IN APPROXIMATE AREA SHOWN.
- 3

THIS INSERT CONTAINS: 40 CAVITIES FOR SIZE 22 SOCKET CONTACTS
- 4

THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.

NON-ENV	GPRBN40SB	1738194-2
ENVIRONMENTAL	GPRBE40SB	1738194-1
REMARKS	DESCRIPTIVE PART NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.C. THOMAS
CHK
K. HOGAN
APVD
K. HOGAN

10-4-10
10-4-10
10-4-10

DIMENSIONS:
mm

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DWN
C.C. THOMAS
CHK
K. HOGAN
APVD
K. HOGAN

10-4-10
10-4-10
10-4-10

TE Connectivity

INSERT ASSEMBLY, SOCKET, ARRANGEMENT 40, KEY B, GPRB

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-1738194

RESTRICTED TO

SCALE
4:1

SHEET
1

OF
1

REV
B

1471-9 (3/11)