








Stripping Dimensions
(2,5 : 1)



NOTES:

- MATERIAL:
ITEM 1 + 3: COPPER ALLOY
ITEM 2: STAINLESS STEEL
- PLATING, MATING AREA: GOLD FLASH over NICKEL
PLATING, TERMINATION SIDE: 160-240µin TIN over 80µin NICKEL
- CRIMPING: USE CRIMP TOOL 360X21079X
WITH TOOL INSERT 36-000430
TURRET POSITION: 12
SELECTOR SETTINGS: 8 FOR AWG 12
7 FOR AWG 14

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance				 dim. in mm		scale: 5:1 (2,5:1)				
										material: see notes				
									date	name	title: HIGH POWER CONTACT MALE CRIMP VERSION 20A FOR AWG 12-14			
								drawn	19.11.13	Strakerjahn				
								appd.	13.12.13	Koch				
								norm						
								d-old	SK0603Z9					
a	Original							dwg no: 17K1A435		DIN- A4				
rev.	description	date	name							sh: 1				
								part no: 17-400233						