


HONEYWELL
PART NUMBER

15AS17-BA

KTH0092

REV	DOCUMENT	CHANGED BY	CHECK
A	0055638	SJK 21AUG09	CMH



NOTES:

A

B

1 - SWITCH CATALOG LISTING: BA-2RV241-A2

SEE INSTALLATION DRAWING FOR APPLICABLE DIMENSIONS,
CHARACTERISTICS AND RATINGS.

DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:				DRAWN		MBH		13AUG09		Honeywell					
				CHECK		MA		13AUG09							
NO PLACESX±- ONE PLACE.X±.030 TWO PLACE.XX±.015 THREE PLACE.XXX±.005 ANGLESX±3° THIRD ANGLE PROJECTION 				THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.						TITLE SWITCH, BRACKET ASSEMBLY					
				INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY						SIZE	TYPE	CAGE CODE	DRAWING NAME		REV
										B	I	-	15AS17-BA		A
				Pro/ENGINEER		3D		SCALE		2:1		SHEET		1 OF 1	