



DFN-8 to DIP-12 SMT Adapter (0.65 mm pitch, 3.0 x 3.0 mm body)

REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		2.20				
B		0.60				
C		0.30				
B2		1.40				
C2		2.30				
D		0.35				
D2		0.40				
E		0.65				
F					0.600	
G					0.100	
H					0.025	




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)