





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		D	REVISED PER ECO-09-017647	29OCT2009	CR	CR



- HOUSING MATERIAL: LCP, 20% GLASS FILLED
COLOR: BLACK
- CONTACT MATERIAL: BRASS
- CONTACT PLATING: 0.002[.000080] MIN TIN OVER
0.001[.000039] MIN NICKEL.
- RATED FOR USE WITH IR REFLOW SOLDER
PROCESSING UP TO 280° C FOR 10 SECONDS MAX.

11	43.56	[1.715]	1-1744055-1
10	39.60	[1.559]	1-1744055-0
9	35.64	[1.403]	1744055-9
8	31.68	[1.247]	1744055-8
7	27.72	[1.091]	1744055-7
6	23.76	[.935]	1744055-6
5	19.80	[.780]	1744055-5
4	15.84	[.624]	1744055-4
3	11.88	[.468]	1744055-3
2	7.92	[.312]	1744055-2
NUMBER OF POSITIONS	mm	[IN]	PART NUMBER
	DIM A ±0.30		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.13 [.005]
4 PLC ± -
ANGLES ± -
FINISH -

DWN
S. HOOVER
01APR04

CHK
J. ELLIS
01APR04

APVD
J. ELLIS
01APR04

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME
HEADER ASSEMBLY-ECONOMY POWER
VERTICAL, HIGH TEMPERATURE
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1744055

RESTRICTED TO
-

SCALE
5:1

SHEET
1

OF
1

REV
D