

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B3		REVIEW PER ECR-18-013174	26/11/2018	ST	TD










TABLE 1(SEE DATA1 G)

TYPE	A	B	C	D
KEYING LOCATION				



- NOTES
- 1.GENERAL TOLERANCES : ±0.2
- 2.MATERIAL : 6/6 NYLON,UL94V-0
- 3.MATERIAL : PC/PET, UL94V-0
- PARTS COMPLY WITH GWT 750
- 4.MATING HDR ASS'Y P/N : 1743330-□
- 5.APPLICABLE CONTACT P/N : 1743457-1
- 6.KEYING LOCATION : TABLE1,DETAIL G

OBSOLETE	1743419-6	D	3	BLUE
	1743419-4	C		YELLOW
	1743419-2	B		RED
	1743419-1	A		NATURAL
OBSOLETE	1743419-6	D	2	BLUE
OBSOLETE	1743419-4	C		YELLOW
	1743419-2	B		RED
	1743419-1	A		NATURAL
	P/N	TYPE	MATERIAL	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SC KIM	-	TE Connectivity	
		CHK BW KANG	-		
DIMENSIONS: mm		APVD JK SONG	-	NAME	
		PRODUCT SPEC 108-61068		250 2 POS P-LOCK REC HSG (11mmn PITCH)	
		APPLICATION SPEC		SIZE	CAGE CODE
MATERIAL		WEIGHT	-	A2	00779
SEE NOTE 2 3		CUSTOMER DRAWING		DRAWING NO	1743419
		SCALE	N/S	SHEET	1 of 1
		REV	B3		