

Han F+B screw-in housing straight-M32



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 513 0102
Specification	Han F+B screw-in housing straight-M32
HARTING eCatalogue	https://b2b.harting.com/09155130102

Identification

Category	Hoods/Housings
Series	Han® F+B
Type of hood/housing	Screw mounted housing
Description of hood/housing	Straight

Version

Cable entry	1x M32
Locking type	Screw locking
Field of application	Connector for food+beverage industry
	Cleaning: For cleaning with high pressure lances, a cleaning distance > 30 cm is recommended in order to avoid mechanical damage to the connector's exterior parts.
Details	Strain relief: A suitable strain relief is required to enable the F+B connector to resist the stress caused e.g. by the daily cleaning of the machinery. DIN VDE 0100-520: 2013-06 defines the stress relief for a connector depending on the outer diameter of the cable.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP67 locked condition IP6K9K acc. to ISO 20653

Material properties

Material (hood/housing)	Polypropylen
Roughness of the surface	≤0.8 µm

Material properties

Colour (hood/housing)	Blue
Material (seal)	EPDM Silicone
Colour (seal)	Blue
Material flammability class acc. to UL 94	HB
EG1935/2004	compliant

Specifications and approvals

Approvals	Ecolab Topactive 200 Ecolab Topactive 500 Ecolab Topax 66 Ecolab Topactive OKTO Ecolab Topax 990 FDA 21 CFR 177.1520 FDA 21 CFR 177.2600
CE	Yes

Commercial data

Packaging size	1
Net weight	16.7 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors