

Set PP Metal receptacle MM GOF adapter



Image is for illustration purposes only. Please refer to product description.

Part number	09 57 468 0500 000
Specification	Set PP Metal receptacle MM GOF adapter
HARTING eCatalogue	https://b2b.harting.com/09574680500000

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	LC duplex
Element	Panel feed trough set
Description of the contact	Multimode
Description of hood/housing	Easy Install

Version

Number of contacts	2
Locking type	PushPull

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥200
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Metal
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	27 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140223790
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)