




- NOTES
- MATERIAL
HOUSING:THERMO PLASTIC (BLACK)
CONTACT:COPPER ALLOY
 - CONTACT FINISH
MATING SIDE:NICKEL PL.ALL OVER GOLD PL.
CT MATING SIDE:NICKEL PL.ALL OVER MATTE TIN PL.
 - APPLIED AC CONTACT P/N
 - APPLIED GND CONTACT P/N
- △ AC: POWER CONTACT (UNLOADED)
GND:GROUND CONTACT (UNLOADED)
DC:SIGNAL CONTACT (PRELOADED)

MT. TYPE:173977-5 CLIMP II TYPE:179228-5	3-292187-2	48.1	43.5	47.9	50.5	17.9	8	21	4	3	DC5 GND1 AC3	4-292190-2
MT. TYPE:173977-5 CLIMP II TYPE:179228-5	1-292187-2	41.1	36.5	40.9	43.5	14.4	8	14	4	2	DC5 GND1 AC2	2-292190-2
APPLIED CT CONN P/N	MATING COUNTER P/N	G	F	E	D	C	B	A	n	N	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

SEE NOTES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

SEE NOTES

DWN J.JIANG 05FEB03

CHK S.YAO 05FEB03

APVD T.SAKAI 05FEB03

PRODUCT SPEC 108-60023

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Shanghai, P.R.China,200233

NAME
HYBRID SF DRAWER CONN.
RECEPTACLE

SIZE A3 CAGE CODE 00779 DRAWING NO C-292190

RESTRICTED TO

SCALE 2:1 SHEET 1 OF 1 REV B