



AMP WIRE RANGE	UL E13288 Listed
16-14 AWG STRANDED	16-14 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE



STAMP AMP 16-14* APPROX AS SHOWN
MAXIMUM LENGTH DOES NOT INCLUDE
MANUFACTURING TABS

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
FOR APPLICATION
TOOLING INFORMATION
FOR ORDER ENTRY

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX
VOLTAGE RATING:
NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE:
1.04-2.62mm² (2,050-5,180 CIR MILS
STRANDED

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN INCHES
TOLERANCES ON:
2 PLG DEC ± .005
3 PLG DEC ± .002
ANGLES
MATERIAL
COPPER PER
ASTM B-152
ANNEALED
FINISH
TIN PLATE
0.00254 [0.00100] MIN
THK PER MIL-T-10727

DR 3-1-93
IA BRINKMAN
CHK 3-1-93
DA PATTERSON
APPD 3-1-93
DE MILLER
APPD 3-1-93
JL HECKLEY
PRODUCT SPEC

NAME
AMP Incorporated
Harrisburg, PA 17125-3508

SIZE
CAGE CODE
00779
DRAWING NO
32464
SCALE
10:1
SHEET
1 OF 1