

SUMMARY

Wires

Low voltage 3



Image is for illustrative purpose only

Series	2P
Termination type	Male solder
IP rating	50
AWG wire size	24.00 - 16.00
Cable Ø	7.30 - 9.20 mm
Status	active
Matching parts	CRB.M03.GLL.C92B

Download

[Request a quote](#)

[Eplan](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	CA*: Straight plug with cable collet
Keying	3 keys (alpha=0, gamma=60; Plug: male contacts; Receptacle: female contacts)
Housing Material	PSU (Polysulfone), gray
Weight	8.45 g

Performance

Configuration	2P.M03 : 3 Low V.
Insulator	L: PEEK for solder contacts
Rated Current	17 Amps

Specifications


Contact Type: Solder
Contact Dia.: 1.6 mm (0.062in)
Bucket Dia.: 1.4 mm (0.055in)
Test voltage (kV rms) Contact-contact: 2.4
Air clearance min.: 1.5 mm
Creepage distance min.: 1.5 mm

Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Endurance (Shell): >1000 mating cycles
Temp (min / max): -50°C / +150°C
F ret (min): 150 N
F ret (max): 250 N
Steam sterilization: 20 times (with potting on rear connection)

DRAWINGS



RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.